

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274650

Luminaire Tested: P3AS20R209830D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209830D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 774.9 lumens
Efficiency: N/A
Efficacy: 28.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274650

CATALOG NUMBER: P3AS20R209830D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274650

CATALOG NUMBER: P3AS20R209830D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	86	78	73	70	85	77	73	70	77	73	70		76	72	70		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	596268
5°	542019
10°	400594
15°	247811
20°	141506
25°	80787
30°	45298
35°	24654
40°	13511
45°	7443
50°	4332
55°	3135
60°	2938
65°	2698
70°	2372
75°	2542
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7443 cd/sqm

TEST NUMBER: P1274650

CATALOG NUMBER: P3AS20R209830D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.2	27.5
10°-20°	304.4	39.3
20°-30°	158.9	20.5
30°-40°	61.4	7.9
40°-50°	19.9	2.6
50°-60°	7.8	1.0
60°-70°	5.2	0.7
70°-80°	3.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.5	87.3
0°-40°	737.9	95.2
0°-60°	765.7	98.8
0°-90°	774.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	774.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2719	
5°	2462	213
15°	1092	304
25°	334	159
35°	92	61
45°	24	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1274650

CATALOG NUMBER: P3AS20R209830D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2719.2
1°	2714.0
2°	2681.8
3°	2632.4
4°	2556.0
5°	2462.4
6°	2351.6
7°	2228.8
8°	2086.6
9°	1948.1
10°	1799.1
12.5°	1430.0
15°	1091.6
17.5°	816.8
20°	606.4
22.5°	449.2
25°	333.9
27.5°	246.3
30°	178.9
32.5°	129.5
35°	92.1
37.5°	66.6
40°	47.2
42.5°	33.7
45°	24.0
47.5°	17.2
50°	12.7
52.5°	9.7
55°	8.2
57.5°	7.5
60°	6.7
62.5°	6.0
65°	5.2
67.5°	4.5
70°	3.7
72.5°	3.7
75°	3.0
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)