

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273793

Luminaire Tested: P3AS09R509830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 235.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273793
CATALOG NUMBER: P3AS09R509830DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1273793

CATALOG NUMBER: P3AS09R509830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69				69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58				58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53				53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50				50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46				46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43				43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47759
5°	47061
10°	44978
15°	41657
20°	37430
25°	32905
30°	27979
35°	22700
40°	17032
45°	10978
50°	5219
55°	4091
60°	3903
65°	3632
70°	3270
75°	2965
80°	2652
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10978 cd/sqm



TEST NUMBER: P1273793
 CATALOG NUMBER: P3AS09R509830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.0	8.5
10°-20°	51.2	21.8
20°-30°	62.2	26.4
30°-40°	52.7	22.4
40°-50°	27.4	11.6
50°-60°	9.9	4.2
60°-70°	6.8	2.9
70°-80°	3.7	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	133.3	56.7
0°-40°	186.0	79.2
0°-60°	223.3	95.0
0°-90°	235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	218	
5°	214	20
15°	184	51
25°	136	62
35°	85	53
45°	35	27
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1273793
CATALOG NUMBER: P3AS09R509830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	217.8
2.5°	217.0
5°	213.8
7.5°	208.9
10°	202.0
12.5°	193.1
15°	183.5
17.5°	172.5
20°	160.4
22.5°	148.1
25°	136.0
27.5°	123.4
30°	110.5
32.5°	97.6
35°	84.8
37.5°	72.1
40°	59.5
42.5°	47.5
45°	35.4
47.5°	23.6
50°	15.3
52.5°	11.8
55°	10.7
57.5°	9.7
60°	8.9
62.5°	7.8
65°	7.0
67.5°	5.9
70°	5.1
72.5°	4.3
75°	3.5
77.5°	2.7
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)