

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273856

Luminaire Tested: P3AS09R609830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 451.0 lumens
Efficiency: N/A
Efficacy: 41.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273856

CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1273856

CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80059
5°	79155
10°	76418
15°	72191
20°	66552
25°	60270
30°	53502
35°	45722
40°	36354
45°	25646
50°	15317
55°	7761
60°	7456
65°	6797
70°	6347
75°	6015
80°	5556
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25646 cd/sqm

TEST NUMBER: P1273856

CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	7.5
10°-20°	88.9	19.7
20°-30°	114.1	25.3
30°-40°	105.8	23.5
40°-50°	64.4	14.3
50°-60°	21.5	4.8
60°-70°	13.1	2.9
70°-80°	7.4	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.8	52.5
0°-40°	342.6	76.0
0°-60°	428.5	95.0
0°-90°	451.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	451.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	365	
5°	360	34
15°	318	89
25°	249	114
35°	171	106
45°	83	64
55°	20	21
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1273856

CATALOG NUMBER: P3AS09R609830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	365.1
2.5°	363.5
5°	359.6
7.5°	352.5
10°	343.2
12.5°	331.7
15°	318.0
17.5°	302.2
20°	285.2
22.5°	267.1
25°	249.1
27.5°	230.4
30°	211.3
32.5°	192.1
35°	170.8
37.5°	148.3
40°	127.0
42.5°	104.5
45°	82.7
47.5°	64.0
50°	44.9
52.5°	26.8
55°	20.3
57.5°	18.6
60°	17.0
62.5°	14.8
65°	13.1
67.5°	11.5
70°	9.9
72.5°	8.2
75°	7.1
77.5°	5.5
80°	4.4
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)