

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273934

Luminaire Tested: P3AS13R159830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 281.0 lumens
Efficiency: N/A
Efficacy: 19.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273934

CATALOG NUMBER: P3AS13R159830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273934

CATALOG NUMBER: P3AS13R159830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70872
5°	68963
10°	63014
15°	55188
20°	47347
25°	39535
30°	31625
35°	23718
40°	17232
45°	11257
50°	7027
55°	4779
60°	4210
65°	3891
70°	3654
75°	3304
80°	3157
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11257 cd/sqm

TEST NUMBER: P1273934

CATALOG NUMBER: P3AS13R159830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	10.3
10°-20°	67.7	24.1
20°-30°	74.6	26.6
30°-40°	55.9	19.9
40°-50°	29.0	10.3
50°-60°	12.0	4.3
60°-70°	7.4	2.6
70°-80°	4.2	1.5
80°-90°	1.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.3	61.0
0°-40°	227.2	80.9
0°-60°	268.1	95.4
0°-90°	281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	323	
5°	313	29
15°	243	68
25°	163	75
35°	89	56
45°	36	29
55°	12	12
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1273934

CATALOG NUMBER: P3AS13R159830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	323.2
1°	323.6
2°	322.5
3°	320.4
4°	317.2
5°	313.3
6°	308.3
7°	302.9
8°	296.5
9°	289.8
10°	283.0
12.5°	263.4
15°	243.1
17.5°	222.8
20°	202.9
22.5°	182.6
25°	163.4
27.5°	144.2
30°	124.9
32.5°	106.1
35°	88.6
37.5°	73.7
40°	60.2
42.5°	47.7
45°	36.3
47.5°	27.4
50°	20.6
52.5°	15.3
55°	12.5
57.5°	11.0
60°	9.6
62.5°	8.5
65°	7.5
67.5°	6.4
70°	5.7
72.5°	4.6
75°	3.9
77.5°	3.2
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.4
90°	0.0

(END OF REPORT)