

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274706

Luminaire Tested: P3AS20R309830D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309830D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1927.9 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274706
CATALOG NUMBER: P3AS20R309830D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1274706
 CATALOG NUMBER: P3AS20R309830D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92	94
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88	90
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	86	85	88
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	83	82	85
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80	82
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78	80
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74	76
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1533978
5°	1513974
10°	1321841
15°	840164
20°	332879
25°	111176
30°	51729
35°	23450
40°	8988
45°	4404
50°	1262
55°	573
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4404 cd/sqm



TEST NUMBER: P1274706
 CATALOG NUMBER: P3AS20R309830D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	628.8	32.6
10°-20°	975.2	50.6
20°-30°	251.4	13.0
30°-40°	59.1	3.1
40°-50°	11.5	0.6
50°-60°	1.3	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1855.4	96.2
0°-40°	1914.5	99.3
0°-60°	1927.3	100.0
0°-90°	1927.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1927.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6996	
5°	6878	629
15°	3701	975
25°	460	251
35°	88	59
45°	14	12
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1274706
CATALOG NUMBER: P3AS20R309830D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	6995.5
1°	6990.3
2°	6973.8
3°	6955.1
4°	6927.4
5°	6878.0
6°	6797.9
7°	6664.7
8°	6482.8
9°	6245.6
10°	5936.5
11°	5569.0
12°	5167.8
13°	4706.1
14°	4222.6
15°	3700.9
16°	3189.8
17°	2697.3
18°	2225.1
19°	1791.7
20°	1426.5
21°	1122.6
22°	883.1
23°	699.0
24°	559.8
25°	459.5
26°	383.2
27°	325.6
28°	281.4
29°	241.0
30°	204.3
32.5°	128.7
35°	87.6
37.5°	54.6
40°	31.4
42.5°	21.0
45°	14.2
47.5°	8.2
50°	3.7
52.5°	1.5
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P1274706
CATALOG NUMBER: P3AS20R309830D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)