

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274765

Luminaire Tested: P3AS20R409830D010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274765  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R409830D010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2146.0 lumens  
Efficiency: N/A  
Efficacy: 78.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274765  
CATALOG NUMBER: P3AS20R409830D010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1274765  
 CATALOG NUMBER: P3AS20R409830D010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	94	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	90	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	86	86	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	83	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	80	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	77	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	75	75	73
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	72	72	71
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	70	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1129931
5°	1124496
10°	1087844
15°	962457
20°	627955
25°	222448
30°	47172
35°	15526
40°	5696
45°	1892
50°	1569
55°	1759
60°	1360
65°	1608
70°	962
75°	1271
80°	1894
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 2520 cd/sqm



TEST NUMBER: P1274765  
 CATALOG NUMBER: P3AS20R409830D010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	480.7	22.4
10°-20°	1119.4	52.2
20°-30°	485.8	22.6
30°-40°	44.8	2.1
40°-50°	6.4	0.3
50°-60°	4.0	0.2
60°-70°	2.9	0.1
70°-80°	1.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2085.9	97.2
0°-40°	2130.6	99.3
0°-60°	2141.0	99.8
0°-90°	2146.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2146.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5153	
5°	5109	481
15°	4240	1119
25°	919	486
35°	58	45
45°	6	6
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1274765  
CATALOG NUMBER: P3AS20R409830D010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5152.9
2.5°	5146.8
5°	5108.6
7.5°	5027.6
10°	4885.6
12.5°	4645.8
15°	4239.6
17.5°	3566.1
20°	2691.0
22.5°	1747.1
25°	919.4
27.5°	395.6
30°	186.3
32.5°	100.8
35°	58.0
37.5°	35.1
40°	19.9
42.5°	10.7
45°	6.1
47.5°	4.6
50°	4.6
52.5°	4.6
55°	4.6
57.5°	4.6
60°	3.1
62.5°	3.1
65°	3.1
67.5°	3.1
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)