

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274766

Luminaire Tested: P3AS20R409830D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409830D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2138.9 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274766
CATALOG NUMBER: P3AS20R409830D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1274766
 CATALOG NUMBER: P3AS20R409830D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	75	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1090307
5°	1082432
10°	1054089
15°	941595
20°	624338
25°	233893
30°	62567
35°	24467
40°	8788
45°	4186
50°	1262
55°	573
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4186 cd/sqm



TEST NUMBER: P1274766
 CATALOG NUMBER: P3AS20R409830D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.1	21.7
10°-20°	1099.0	51.4
20°-30°	498.4	23.3
30°-40°	64.6	3.0
40°-50°	11.2	0.5
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2061.4	96.4
0°-40°	2126.0	99.4
0°-60°	2138.5	100.0
0°-90°	2138.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2138.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4972	
5°	4918	464
15°	4148	1099
25°	967	498
35°	91	65
45°	14	11
55°	2	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1274766
CATALOG NUMBER: P3AS20R409830D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4972.2
1°	4969.2
2°	4961.7
3°	4950.4
4°	4936.2
5°	4917.5
6°	4895.8
7°	4868.8
8°	4835.9
9°	4790.9
10°	4734.0
11°	4667.4
12°	4578.3
13°	4468.2
14°	4324.4
15°	4147.7
16°	3922.3
17°	3665.5
18°	3357.0
19°	3031.2
20°	2675.5
21°	2319.8
22°	1969.4
23°	1620.4
24°	1277.5
25°	966.7
26°	715.9
27°	524.2
28°	393.9
29°	306.3
30°	247.1
31°	204.4
32°	170.7
32.5°	155.8
33°	140.8
34°	114.6
35°	91.4
36°	71.9
37°	56.9
37.5°	50.9
38°	44.9
39°	37.4
40°	30.7
42.5°	20.2
45°	13.5



TEST NUMBER: P1274766
CATALOG NUMBER: P3AS20R409830D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	8.2
50°	3.7
52.5°	1.5
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)