

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274793

Luminaire Tested: P3AS20R459830D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459830D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 837.0 lumens
Efficiency: N/A
Efficacy: 30.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274793

CATALOG NUMBER: P3AS20R459830D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274793

CATALOG NUMBER: P3AS20R459830D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314317
5°	306955
10°	282181
15°	239093
20°	185493
25°	129661
30°	81683
35°	48078
40°	27222
45°	13242
50°	4605
55°	3708
60°	3596
65°	3476
70°	3334
75°	3135
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13242 cd/sqm

TEST NUMBER: P1274793

CATALOG NUMBER: P3AS20R459830D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	15.4
10°-20°	289.2	34.6
20°-30°	245.6	29.3
30°-40°	117.1	14.0
40°-50°	35.3	4.2
50°-60°	8.9	1.1
60°-70°	6.7	0.8
70°-80°	3.9	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.9	79.3
0°-40°	781.0	93.3
0°-60°	825.3	98.6
0°-90°	837.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	837.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1433	
5°	1394	129
15°	1053	289
25°	536	246
35°	180	117
45°	43	35
55°	10	9
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1274793

CATALOG NUMBER: P3AS20R459830D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1433.4
2.5°	1424.4
5°	1394.5
7.5°	1342.9
10°	1267.3
12.5°	1167.0
15°	1053.2
17.5°	926.7
20°	794.9
22.5°	660.9
25°	535.9
27.5°	422.2
30°	322.6
32.5°	242.5
35°	179.6
37.5°	132.5
40°	95.1
42.5°	65.9
45°	42.7
47.5°	24.0
50°	13.5
52.5°	10.5
55°	9.7
57.5°	9.0
60°	8.2
62.5°	7.5
65°	6.7
67.5°	6.0
70°	5.2
72.5°	4.5
75°	3.7
77.5°	3.0
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)