

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274032

Luminaire Tested: P3AS13R309830DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274032
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309830DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 468.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274032
CATALOG NUMBER: P3AS13R309830DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1274032
 CATALOG NUMBER: P3AS13R309830DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159921
5°	154941
10°	139610
15°	115483
20°	89421
25°	67068
30°	48691
35°	32444
40°	19952
45°	11691
50°	7164
55°	5811
60°	5087
65°	4151
70°	3719
75°	3728
80°	2778
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11691 cd/sqm



TEST NUMBER: P1274032
 CATALOG NUMBER: P3AS13R309830DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	13.8
10°-20°	140.1	29.9
20°-30°	127.5	27.2
30°-40°	77.1	16.5
40°-50°	30.9	6.6
50°-60°	13.7	2.9
60°-70°	8.3	1.8
70°-80°	4.5	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.3	71.0
0°-40°	409.4	87.5
0°-60°	454.0	97.0
0°-90°	468.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	468.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	729	
5°	704	65
15°	509	140
25°	277	127
35°	121	77
45°	38	31
55°	15	14
65°	8	8
75°	4	5
85°	2	1
90°	0	



TEST NUMBER: P1274032
CATALOG NUMBER: P3AS13R309830DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	729.3
1°	728.6
2°	725.7
3°	720.6
4°	713.3
5°	703.9
6°	692.3
7°	680.0
8°	664.0
9°	645.9
10°	627.0
11°	605.2
12°	582.0
13°	558.8
14°	533.4
15°	508.7
17.5°	444.1
20°	383.2
22.5°	326.6
25°	277.2
27.5°	232.2
30°	192.3
32.5°	155.3
35°	121.2
37.5°	92.9
40°	69.7
42.5°	50.8
45°	37.7
47.5°	28.3
50°	21.0
52.5°	16.7
55°	15.2
57.5°	13.1
60°	11.6
62.5°	9.4
65°	8.0
67.5°	7.3
70°	5.8
72.5°	5.1
75°	4.4
77.5°	3.6
80°	2.2
82.5°	1.5
85°	1.5
87.5°	0.7



TEST NUMBER: P1274032
CATALOG NUMBER: P3AS13R309830DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)