

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274814

Luminaire Tested: P3AS20R509830D010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509830D010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2091.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274814

CATALOG NUMBER: P3AS20R509830D010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1274814

CATALOG NUMBER: P3AS20R509830D010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	728231
5°	715208
10°	686716
15°	629720
20°	555288
25°	425613
30°	231403
35°	74472
40°	17490
45°	2357
50°	2081
55°	2332
60°	2017
65°	2387
70°	1988
75°	2626
80°	1894
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 3774 cd/sqm

TEST NUMBER: P1274814

CATALOG NUMBER: P3AS20R509830D010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.9	14.6
10°-20°	771.1	36.9
20°-30°	772.2	36.9
30°-40°	217.1	10.4
40°-50°	13.1	0.6
50°-60°	5.0	0.2
60°-70°	4.0	0.2
70°-80°	2.6	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1848.2	88.4
0°-40°	2065.3	98.8
0°-60°	2083.4	99.6
0°-90°	2091.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2091.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3321	
5°	3249	305
15°	2774	771
25°	1759	772
35°	278	217
45°	8	13
55°	6	5
65°	5	4
75°	3	3
85°	2	1
90°	0	

TEST NUMBER: P1274814

CATALOG NUMBER: P3AS20R509830D010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3321.0
2.5°	3304.2
5°	3249.2
7.5°	3174.3
10°	3084.1
12.5°	2948.1
15°	2773.9
17.5°	2573.7
20°	2379.6
22.5°	2138.1
25°	1759.1
27.5°	1309.8
30°	913.9
32.5°	551.7
35°	278.2
37.5°	131.4
40°	61.1
42.5°	22.9
45°	7.6
47.5°	6.1
50°	6.1
52.5°	6.1
55°	6.1
57.5°	4.6
60°	4.6
62.5°	4.6
65°	4.6
67.5°	3.1
70°	3.1
72.5°	3.1
75°	3.1
77.5°	1.5
80°	1.5
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0

(END OF REPORT)