

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274076

Luminaire Tested: P3AS13R409830DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409830DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1016.0 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274076
CATALOG NUMBER: P3AS13R409830DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1274076
 CATALOG NUMBER: P3AS13R409830DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	94	94	94	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	90	90	90	88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	86	86	86	85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	83	83	83	82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	80	80	80	79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	77	77	77	76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	74	74	74	73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	71	71	71	70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	69	69	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	517875
5°	514152
10°	500681
15°	447244
20°	296546
25°	111103
30°	29726
35°	11618
40°	4179
45°	1985
50°	614
55°	268
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1985 cd/sqm



TEST NUMBER: P1274076
 CATALOG NUMBER: P3AS13R409830DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.4	21.7
10°-20°	522.0	51.4
20°-30°	236.7	23.3
30°-40°	30.7	3.0
40°-50°	5.3	0.5
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	979.2	96.4
0°-40°	1009.8	99.4
0°-60°	1015.8	100.0
0°-90°	1016.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1016.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2362	
5°	2336	220
15°	1970	522
25°	459	237
35°	43	31
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1274076
CATALOG NUMBER: P3AS13R409830DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2361.7
1°	2360.3
2°	2356.7
3°	2351.4
4°	2344.6
5°	2335.8
6°	2325.4
7°	2312.6
8°	2297.0
9°	2275.6
10°	2248.6
11°	2217.0
12°	2174.6
13°	2122.3
14°	2054.1
15°	1970.1
16°	1863.1
17°	1741.1
18°	1594.5
19°	1439.8
20°	1270.8
21°	1101.9
22°	935.4
23°	769.7
24°	606.8
25°	459.2
26°	340.0
27°	249.0
28°	187.1
29°	145.5
30°	117.4
31°	97.1
32°	81.1
32.5°	74.0
33°	66.9
34°	54.4
35°	43.4
36°	34.1
37°	27.0
37.5°	24.2
38°	21.3
39°	17.8
40°	14.6
42.5°	9.6
45°	6.4



TEST NUMBER: P1274076
CATALOG NUMBER: P3AS13R409830DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	3.9
50°	1.8
52.5°	0.7
55°	0.7
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)