

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274083

Luminaire Tested: P3AS13R409830DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274083
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409830DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.0 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274083

CATALOG NUMBER: P3AS13R409830DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1274083

CATALOG NUMBER: P3AS13R409830DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	373895
5°	363041
10°	329453
15°	272170
20°	196320
25°	121434
30°	65757
35°	33970
40°	18492
45°	10358
50°	5185
55°	3900
60°	3508
65°	3373
70°	3270
75°	3050
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10358 cd/sqm

TEST NUMBER: P1274083

CATALOG NUMBER: P3AS13R409830DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.0	18.0
10°-20°	326.5	38.6
20°-30°	233.0	27.6
30°-40°	85.8	10.1
40°-50°	27.0	3.2
50°-60°	9.4	1.1
60°-70°	6.5	0.8
70°-80°	3.8	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.5	84.2
0°-40°	797.2	94.3
0°-60°	833.6	98.7
0°-90°	845.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1705	
5°	1649	152
15°	1199	326
25°	502	233
35°	127	86
45°	33	27
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1274083

CATALOG NUMBER: P3AS13R409830DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1705.1
2.5°	1692.1
5°	1649.3
7.5°	1578.2
10°	1479.6
12.5°	1354.1
15°	1198.9
17.5°	1024.8
20°	841.3
22.5°	660.7
25°	501.9
27.5°	368.4
30°	259.7
32.5°	182.0
35°	126.9
37.5°	89.9
40°	64.6
42.5°	46.4
45°	33.4
47.5°	22.5
50°	15.2
52.5°	10.9
55°	10.2
57.5°	9.4
60°	8.0
62.5°	7.3
65°	6.5
67.5°	5.8
70°	5.1
72.5°	4.4
75°	3.6
77.5°	2.9
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)