

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274103

Luminaire Tested: P3AS13R459830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 398.0 lumens
Efficiency: N/A
Efficacy: 27.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274103

CATALOG NUMBER: P3AS13R459830DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274103

CATALOG NUMBER: P3AS13R459830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149462
5°	145960
10°	134177
15°	113690
20°	88208
25°	61649
30°	38841
35°	22861
40°	12939
45°	6295
50°	2183
55°	1759
60°	1710
65°	1660
70°	1603
75°	1525
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6295 cd/sqm

TEST NUMBER: P1274103

CATALOG NUMBER: P3AS13R459830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	15.4
10°-20°	137.5	34.6
20°-30°	116.8	29.3
30°-40°	55.7	14.0
40°-50°	16.8	4.2
50°-60°	4.3	1.1
60°-70°	3.2	0.8
70°-80°	1.9	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	315.7	79.3
0°-40°	371.4	93.3
0°-60°	392.4	98.6
0°-90°	398.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	398.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	682	
5°	663	61
15°	501	138
25°	255	117
35°	85	56
45°	20	17
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1274103

CATALOG NUMBER: P3AS13R459830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	681.6
2.5°	677.3
5°	663.1
7.5°	638.5
10°	602.6
12.5°	554.9
15°	500.8
17.5°	440.6
20°	378.0
22.5°	314.3
25°	254.8
27.5°	200.7
30°	153.4
32.5°	115.3
35°	85.4
37.5°	63.0
40°	45.2
42.5°	31.3
45°	20.3
47.5°	11.4
50°	6.4
52.5°	5.0
55°	4.6
57.5°	4.3
60°	3.9
62.5°	3.6
65°	3.2
67.5°	2.8
70°	2.5
72.5°	2.1
75°	1.8
77.5°	1.4
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)