

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274866

Luminaire Tested: P3AS20R559830D010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559830D010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1111.0 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274866

CATALOG NUMBER: P3AS20R559830D010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1274866

CATALOG NUMBER: P3AS20R559830D010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79		
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55		
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52		
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302235
5°	294650
10°	273921
15°	243929
20°	207288
25°	167284
30°	127539
35°	90694
40°	59855
45°	35508
50°	20844
55°	12845
60°	11359
65°	10273
70°	8784
75°	7795
80°	7703
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35508 cd/sqm

TEST NUMBER: P1274866

CATALOG NUMBER: P3AS20R559830D010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.3	11.2
10°-20°	297.9	26.8
20°-30°	315.5	28.4
30°-40°	213.2	19.2
40°-50°	93.4	8.4
50°-60°	33.4	3.0
60°-70°	19.6	1.8
70°-80°	10.3	0.9
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	737.7	66.4
0°-40°	950.9	85.6
0°-60°	1077.8	97.0
0°-90°	1111.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1111.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1378	
5°	1339	124
15°	1074	298
25°	691	316
35°	339	213
45°	114	93
55°	34	33
65°	20	20
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P1274866

CATALOG NUMBER: P3AS20R559830D010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1378.3
2.5°	1367.6
5°	1338.6
7.5°	1291.3
10°	1230.2
12.5°	1156.9
15°	1074.5
17.5°	982.9
20°	888.3
22.5°	789.1
25°	691.4
27.5°	595.3
30°	503.7
32.5°	416.7
35°	338.8
37.5°	268.6
40°	209.1
42.5°	157.2
45°	114.5
47.5°	83.9
50°	61.1
52.5°	42.7
55°	33.6
57.5°	30.5
60°	25.9
62.5°	22.9
65°	19.8
67.5°	16.8
70°	13.7
72.5°	12.2
75°	9.2
77.5°	7.6
80°	6.1
82.5°	4.6
85°	3.1
87.5°	1.5
90°	0.0

(END OF REPORT)