

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274109

Luminaire Tested: P3AS13R459830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 309.0 lumens
Efficiency: N/A
Efficacy: 21.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274109

CATALOG NUMBER: P3AS13R459830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274109

CATALOG NUMBER: P3AS13R459830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65521
5°	64363
10°	60898
15°	55528
20°	49121
25°	42656
30°	36613
35°	30517
40°	22728
45°	13924
50°	6448
55°	5046
60°	4824
65°	4410
70°	4103
75°	3897
80°	3536
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13924 cd/sqm

TEST NUMBER: P1274109

CATALOG NUMBER: P3AS13R459830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.3	8.8
10°-20°	68.1	22.0
20°-30°	80.9	26.2
30°-40°	70.3	22.8
40°-50°	35.3	11.4
50°-60°	12.2	4.0
60°-70°	8.6	2.8
70°-80°	4.8	1.5
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.4	57.1
0°-40°	246.7	79.8
0°-60°	294.2	95.2
0°-90°	309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	299	
5°	292	27
15°	245	68
25°	176	81
35°	114	70
45°	45	35
55°	13	12
65°	8	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1274109

CATALOG NUMBER: P3AS13R459830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	298.8
2.5°	297.3
5°	292.4
7.5°	284.5
10°	273.5
12.5°	260.0
15°	244.6
17.5°	227.6
20°	210.5
22.5°	193.0
25°	176.3
27.5°	160.2
30°	144.6
32.5°	129.6
35°	114.0
37.5°	97.2
40°	79.4
42.5°	62.0
45°	44.9
47.5°	29.6
50°	18.9
52.5°	14.6
55°	13.2
57.5°	12.1
60°	11.0
62.5°	10.0
65°	8.5
67.5°	7.5
70°	6.4
72.5°	5.3
75°	4.6
77.5°	3.6
80°	2.8
82.5°	2.1
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)