

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274131

Luminaire Tested: P3AS13R509830DE010 E3D1WMH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274131  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R509830DE010 E3D1WMH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1008.1 lumens  
Efficiency: N/A  
Efficacy: 69.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274131  
CATALOG NUMBER: P3AS13R509830DE010 E3D1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1274131  
 CATALOG NUMBER: P3AS13R509830DE010 E3D1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	74	70	67	74	69	66	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	352252
5°	342878
10°	327204
15°	296211
20°	256269
25°	210206
30°	120753
35°	37504
40°	10076
45°	3535
50°	853
55°	268
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3535 cd/sqm



TEST NUMBER: P1274131  
 CATALOG NUMBER: P3AS13R509830DE010 E3D1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.9	14.5
10°-20°	361.5	35.9
20°-30°	380.0	37.7
30°-40°	108.8	10.8
40°-50°	10.6	1.1
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.4	88.0
0°-40°	996.2	98.8
0°-60°	1007.7	100.0
0°-90°	1008.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1606	
5°	1558	146
15°	1305	362
25°	869	380
35°	140	109
45°	11	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1274131  
CATALOG NUMBER: P3AS13R509830DE010 E3D1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1606.4
1°	1603.9
2°	1596.8
3°	1586.5
4°	1572.6
5°	1557.7
6°	1541.7
7°	1524.6
8°	1508.6
9°	1490.1
10°	1469.5
11°	1445.7
12°	1418.3
13°	1384.1
14°	1347.2
15°	1304.8
16°	1260.0
17°	1216.6
18°	1172.2
19°	1133.1
20°	1098.2
21°	1064.8
22°	1026.7
23°	983.0
24°	931.8
25°	868.8
26°	800.5
27°	724.4
28°	648.7
29°	566.9
30°	476.9
31°	392.6
32°	315.1
32.5°	281.3
33°	247.2
34°	189.6
35°	140.1
36°	102.8
37°	76.5
37.5°	66.1
38°	57.3
39°	44.5
40°	35.2
42.5°	19.9
45°	11.4



TEST NUMBER: P1274131  
CATALOG NUMBER: P3AS13R509830DE010 E3D1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	6.4
50°	2.5
52.5°	1.1
55°	0.7
57.5°	0.7
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)