

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274911

Luminaire Tested: P3AS20R659830D010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274911
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659830D010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1532.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274911
CATALOG NUMBER: P3AS20R659830D010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1274911

CATALOG NUMBER: P3AS20R659830D010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	361287
5°	356966
10°	343414
15°	321682
20°	289335
25°	245675
30°	192156
35°	136925
40°	89596
45°	55417
50°	28144
55°	9940
60°	8727
65°	8717
70°	7822
75°	7795
80°	7703
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55417 cd/sqm



TEST NUMBER: P1274911

CATALOG NUMBER: P3AS20R659830D010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.3	9.9
10°-20°	394.4	25.7
20°-30°	460.9	30.1
30°-40°	322.1	21.0
40°-50°	141.8	9.3
50°-60°	31.6	2.1
60°-70°	16.0	1.0
70°-80°	9.7	0.6
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1007.5	65.8
0°-40°	1329.6	86.8
0°-60°	1503.0	98.1
0°-90°	1532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1532.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1648	
5°	1622	152
15°	1417	394
25°	1015	461
35°	512	322
45°	179	142
55°	26	32
65°	17	16
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P1274911
CATALOG NUMBER: P3AS20R659830D010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1647.6
2.5°	1641.5
5°	1621.7
7.5°	1588.1
10°	1542.3
12.5°	1485.8
15°	1417.0
17.5°	1333.1
20°	1239.9
22.5°	1134.5
25°	1015.4
27.5°	890.2
30°	758.9
32.5°	632.2
35°	511.5
37.5°	406.2
40°	313.0
42.5°	236.7
45°	178.7
47.5°	131.3
50°	82.5
52.5°	42.8
55°	26.0
57.5°	22.9
60°	19.9
62.5°	18.3
65°	16.8
67.5°	13.7
70°	12.2
72.5°	10.7
75°	9.2
77.5°	7.6
80°	6.1
82.5°	4.6
85°	3.1
87.5°	1.5
90°	0.0

(END OF REPORT)