

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274139

Luminaire Tested: P3AS13R509830DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274139  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R509830DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 636.0 lumens  
Efficiency: N/A  
Efficacy: 43.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274139  
CATALOG NUMBER: P3AS13R509830DE010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1274139  
 CATALOG NUMBER: P3AS13R509830DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	129244
5°	127338
10°	121708
15°	112713
20°	101299
25°	89037
30°	75733
35°	61409
40°	46115
45°	29709
50°	14123
55°	11087
60°	10525
65°	9806
70°	8848
75°	7964
80°	7324
85°	7296

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29709 cd/sqm



TEST NUMBER: P1274139  
 CATALOG NUMBER: P3AS13R509830DE010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.2	8.5
10°-20°	138.4	21.8
20°-30°	168.2	26.4
30°-40°	142.6	22.4
40°-50°	74.1	11.6
50°-60°	26.7	4.2
60°-70°	18.5	2.9
70°-80°	10.0	1.6
80°-90°	3.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.8	56.7
0°-40°	503.5	79.2
0°-60°	604.3	95.0
0°-90°	636.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	636.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	589	
5°	578	54
15°	496	138
25°	368	168
35°	229	143
45°	96	74
55°	29	27
65°	19	19
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P1274139  
CATALOG NUMBER: P3AS13R509830DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	589.4
2.5°	587.2
5°	578.5
7.5°	565.5
10°	546.6
12.5°	522.6
15°	496.5
17.5°	466.7
20°	434.1
22.5°	400.7
25°	368.0
27.5°	333.9
30°	299.1
32.5°	264.2
35°	229.4
37.5°	195.3
40°	161.1
42.5°	128.5
45°	95.8
47.5°	63.9
50°	41.4
52.5°	31.9
55°	29.0
57.5°	26.1
60°	24.0
62.5°	21.1
65°	18.9
67.5°	16.0
70°	13.8
72.5°	11.6
75°	9.4
77.5°	7.3
80°	5.8
82.5°	4.4
85°	2.9
87.5°	1.5
90°	0.0

(END OF REPORT)