

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274164

Luminaire Tested: P3AS13R559830DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274164
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559830DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 791.0 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274164
CATALOG NUMBER: P3AS13R559830DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1274164
 CATALOG NUMBER: P3AS13R559830DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217198
5°	214990
10°	207634
15°	191919
20°	165611
25°	130798
30°	92799
35°	59829
40°	35924
45°	20250
50°	10882
55°	3900
60°	3508
65°	3373
70°	3270
75°	3050
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20250 cd/sqm



TEST NUMBER: P1274164
 CATALOG NUMBER: P3AS13R559830DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.9	11.6
10°-20°	233.8	29.6
20°-30°	245.0	31.0
30°-40°	142.9	18.1
40°-50°	53.5	6.8
50°-60°	12.6	1.6
60°-70°	6.5	0.8
70°-80°	3.8	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.6	72.1
0°-40°	713.6	90.2
0°-60°	779.6	98.6
0°-90°	791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	791.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	990	
5°	977	92
15°	845	234
25°	541	245
35°	224	143
45°	65	53
55°	10	13
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1274164
CATALOG NUMBER: P3AS13R559830DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	990.5
2.5°	987.6
5°	976.7
7.5°	959.3
10°	932.5
12.5°	894.7
15°	845.4
17.5°	783.0
20°	709.7
22.5°	627.7
25°	540.6
27.5°	451.4
30°	366.5
32.5°	289.5
35°	223.5
37.5°	169.8
40°	125.5
42.5°	90.0
45°	65.3
47.5°	47.2
50°	31.9
52.5°	18.1
55°	10.2
57.5°	8.7
60°	8.0
62.5°	7.3
65°	6.5
67.5°	5.8
70°	5.1
72.5°	4.4
75°	3.6
77.5°	2.9
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)