

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274938

Luminaire Tested: P3AS20R709830D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709830D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 753.9 lumens
Efficiency: N/A
Efficacy: 27.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274938

CATALOG NUMBER: P3AS20R709830D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274938

CATALOG NUMBER: P3AS20R709830D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145975
5°	144222
10°	140055
15°	134121
20°	125638
25°	114128
30°	98597
35°	78568
40°	57221
45°	37616
50°	17637
55°	5429
60°	5263
65°	5033
70°	4809
75°	5083
80°	4672
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37616 cd/sqm

TEST NUMBER: P1274938

CATALOG NUMBER: P3AS20R709830D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	8.2
10°-20°	165.3	21.9
20°-30°	214.9	28.5
30°-40°	182.3	24.2
40°-50°	94.0	12.5
50°-60°	18.1	2.4
60°-70°	9.8	1.3
70°-80°	6.0	0.8
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.9	58.6
0°-40°	624.3	82.8
0°-60°	736.4	97.7
0°-90°	753.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	753.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	655	62
15°	591	165
25°	472	215
35°	294	182
45°	121	94
55°	14	18
65°	10	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1274938

CATALOG NUMBER: P3AS20R709830D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	665.7
2.5°	663.4
5°	655.2
7.5°	643.2
10°	629.0
12.5°	611.0
15°	590.8
17.5°	566.1
20°	538.4
22.5°	506.9
25°	471.7
27.5°	432.0
30°	389.4
32.5°	342.2
35°	293.5
37.5°	245.6
40°	199.9
42.5°	157.2
45°	121.3
47.5°	89.1
50°	51.7
52.5°	22.5
55°	14.2
57.5°	13.5
60°	12.0
62.5°	11.2
65°	9.7
67.5°	9.0
70°	7.5
72.5°	6.7
75°	6.0
77.5°	4.5
80°	3.7
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)