

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274983

Luminaire Tested: P3AS02R159835DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159835DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 87.0 lumens
Efficiency: N/A
Efficacy: 24.2 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274983

CATALOG NUMBER: P3AS02R159835DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1274983

CATALOG NUMBER: P3AS02R159835DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	67	76	70	66		74	69	65		72
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32563
5°	29892
10°	23825
15°	17798
20°	13511
25°	10234
30°	7571
35°	5407
40°	3693
45°	2605
50°	2217
55°	2179
60°	2237
65°	2387
70°	2436
75°	2542
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 3192 cd/sqm

TEST NUMBER: P1274983

CATALOG NUMBER: P3AS02R159835DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.0	13.8
10°-20°	22.0	25.3
20°-30°	19.5	22.4
30°-40°	12.8	14.7
40°-50°	6.8	7.8
50°-60°	5.2	5.9
60°-70°	4.4	5.1
70°-80°	3.1	3.5
80°-90°	1.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	53.5	61.5
0°-40°	66.3	76.2
0°-60°	78.3	89.9
0°-90°	87.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	87.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	148	
5°	136	12
15°	78	22
25°	42	19
35°	20	13
45°	8	7
55°	6	5
65°	5	4
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1274983

CATALOG NUMBER: P3AS02R159835DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	148.5
2.5°	145.0
5°	135.8
7.5°	122.4
10°	107.0
12.5°	92.2
15°	78.4
17.5°	67.4
20°	57.9
22.5°	49.6
25°	42.3
27.5°	35.8
30°	29.9
32.5°	24.8
35°	20.2
37.5°	16.2
40°	12.9
42.5°	10.2
45°	8.4
47.5°	7.3
50°	6.5
52.5°	6.2
55°	5.7
57.5°	5.4
60°	5.1
62.5°	4.9
65°	4.6
67.5°	4.0
70°	3.8
72.5°	3.2
75°	3.0
77.5°	2.4
80°	2.2
82.5°	1.9
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)