

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275004

Luminaire Tested: P3AS02R209835DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209835DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 147.0 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275004
CATALOG NUMBER: P3AS02R209835DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1275004

CATALOG NUMBER: P3AS02R209835DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 95 | 93 | 91 | | | | 91 |
| 2 | 106 | 100 | 96 | 92 | 104 | 99 | 94 | 91 | 95 | 92 | 89 | 92 | 89 | 87 | 90 | 87 | 85 | 83 | | | | 83 |
| 3 | 100 | 93 | 87 | 82 | 98 | 91 | 86 | 82 | 88 | 84 | 80 | 86 | 82 | 79 | 84 | 81 | 78 | 76 | | | | 76 |
| 4 | 94 | 86 | 79 | 75 | 92 | 85 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | | | | 70 |
| 5 | 89 | 80 | 73 | 68 | 87 | 79 | 73 | 68 | 77 | 71 | 67 | 75 | 70 | 67 | 73 | 69 | 66 | 65 | | | | 65 |
| 6 | 84 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 61 | 60 | | | | 60 |
| 7 | 80 | 69 | 63 | 58 | 78 | 69 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 57 | 65 | 60 | 57 | 55 | | | | 55 |
| 8 | 75 | 65 | 59 | 54 | 74 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 53 | 61 | 57 | 53 | 52 | | | | 52 |
| 9 | 72 | 61 | 55 | 50 | 70 | 61 | 55 | 50 | 60 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 50 | 48 | | | | 48 |
| 10 | 68 | 58 | 51 | 47 | 67 | 57 | 51 | 47 | 56 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 45 | | | | 45 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 36357 |
| 5° | 35395 |
| 10° | 32553 |
| 15° | 28649 |
| 20° | 24572 |
| 25° | 20638 |
| 30° | 16686 |
| 35° | 12689 |
| 40° | 9046 |
| 45° | 5954 |
| 50° | 3684 |
| 55° | 2409 |
| 60° | 2193 |
| 65° | 2024 |
| 70° | 1923 |
| 75° | 1779 |
| 80° | 1642 |
| 85° | 1510 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5954 cd/sqm



TEST NUMBER: P1275004
 CATALOG NUMBER: P3AS02R209835DE010 E3DLD1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 14.9 | 10.1 |
| 10°-20° | 35.1 | 23.9 |
| 20°-30° | 39.0 | 26.5 |
| 30°-40° | 29.8 | 20.2 |
| 40°-50° | 15.2 | 10.4 |
| 50°-60° | 6.2 | 4.2 |
| 60°-70° | 3.9 | 2.7 |
| 70°-80° | 2.2 | 1.5 |
| 80°-90° | 0.6 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 89.0 | 60.6 |
| 0°-40° | 118.8 | 80.8 |
| 0°-60° | 140.2 | 95.4 |
| 0°-90° | 147.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 147.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 166 | |
| 5° | 161 | 15 |
| 15° | 126 | 35 |
| 25° | 85 | 39 |
| 35° | 47 | 30 |
| 45° | 19 | 15 |
| 55° | 6 | 6 |
| 65° | 4 | 4 |
| 75° | 2 | 2 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1275004
CATALOG NUMBER: P3AS02R209835DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 165.8 |
| 1° | 166.0 |
| 2° | 165.3 |
| 3° | 164.3 |
| 4° | 162.8 |
| 5° | 160.8 |
| 6° | 158.3 |
| 7° | 155.7 |
| 8° | 152.9 |
| 9° | 149.6 |
| 10° | 146.2 |
| 12.5° | 136.5 |
| 15° | 126.2 |
| 17.5° | 115.8 |
| 20° | 105.3 |
| 22.5° | 94.9 |
| 25° | 85.3 |
| 27.5° | 75.8 |
| 30° | 65.9 |
| 32.5° | 56.6 |
| 35° | 47.4 |
| 37.5° | 39.4 |
| 40° | 31.6 |
| 42.5° | 24.8 |
| 45° | 19.2 |
| 47.5° | 14.6 |
| 50° | 10.8 |
| 52.5° | 8.0 |
| 55° | 6.3 |
| 57.5° | 5.8 |
| 60° | 5.0 |
| 62.5° | 4.5 |
| 65° | 3.9 |
| 67.5° | 3.4 |
| 70° | 3.0 |
| 72.5° | 2.4 |
| 75° | 2.1 |
| 77.5° | 1.7 |
| 80° | 1.3 |
| 82.5° | 0.9 |
| 85° | 0.6 |
| 87.5° | 0.2 |
| 90° | 0.0 |

(END OF REPORT)