

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274192

Luminaire Tested: P3AS13R609830DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609830DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 763.1 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274192
CATALOG NUMBER: P3AS13R609830DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1274192
 CATALOG NUMBER: P3AS13R609830DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68	68	68	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63	63	63	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59	59	59	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55	55	55	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	180161
5°	178472
10°	173254
15°	162316
20°	143676
25°	120200
30°	94192
35°	68342
40°	45457
45°	28344
50°	15351
55°	4435
60°	4122
65°	3788
70°	3719
75°	3728
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28344 cd/sqm



TEST NUMBER: P1274192
 CATALOG NUMBER: P3AS13R609830DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	10.0
10°-20°	198.4	26.0
20°-30°	226.1	29.6
30°-40°	160.4	21.0
40°-50°	72.8	9.5
50°-60°	15.4	2.0
60°-70°	7.4	1.0
70°-80°	4.6	0.6
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.8	65.6
0°-40°	661.2	86.7
0°-60°	749.4	98.2
0°-90°	763.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	763.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	822	
5°	811	76
15°	715	198
25°	497	226
35°	255	160
45°	91	73
55°	12	15
65°	7	7
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P1274192
CATALOG NUMBER: P3AS13R609830DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	821.6
2.5°	818.7
5°	810.8
7.5°	797.0
10°	778.1
12.5°	751.3
15°	715.0
17.5°	669.3
20°	615.7
22.5°	557.7
25°	496.8
27.5°	434.4
30°	372.0
32.5°	312.6
35°	255.3
37.5°	204.5
40°	158.8
42.5°	120.4
45°	91.4
47.5°	68.2
50°	45.0
52.5°	21.0
55°	11.6
57.5°	10.2
60°	9.4
62.5°	8.7
65°	7.3
67.5°	6.5
70°	5.8
72.5°	5.1
75°	4.4
77.5°	3.6
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)