

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274219

Luminaire Tested: P3AS13R659830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 357.0 lumens
Efficiency: N/A
Efficacy: 24.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274219

CATALOG NUMBER: P3AS13R659830DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274219

CATALOG NUMBER: P3AS13R659830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84182
5°	83183
10°	80025
15°	74961
20°	67416
25°	57245
30°	44766
35°	31909
40°	20868
45°	12901
50°	6550
55°	2294
60°	2017
65°	2024
70°	1795
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12901 cd/sqm

TEST NUMBER: P1274219

CATALOG NUMBER: P3AS13R659830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.5	9.9
10°-20°	91.9	25.7
20°-30°	107.4	30.1
30°-40°	75.1	21.0
40°-50°	33.0	9.3
50°-60°	7.3	2.1
60°-70°	3.7	1.0
70°-80°	2.2	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.8	65.8
0°-40°	309.8	86.8
0°-60°	350.2	98.1
0°-90°	357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	378	35
15°	330	92
25°	237	107
35°	119	75
45°	42	33
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1274219

CATALOG NUMBER: P3AS13R659830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	383.9
2.5°	382.5
5°	377.9
7.5°	370.1
10°	359.4
12.5°	346.2
15°	330.2
17.5°	310.6
20°	288.9
22.5°	264.4
25°	236.6
27.5°	207.4
30°	176.8
32.5°	147.3
35°	119.2
37.5°	94.7
40°	72.9
42.5°	55.2
45°	41.6
47.5°	30.6
50°	19.2
52.5°	10.0
55°	6.0
57.5°	5.3
60°	4.6
62.5°	4.3
65°	3.9
67.5°	3.2
70°	2.8
72.5°	2.5
75°	2.1
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)