

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275018

Luminaire Tested: P3AS02R259835DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1275018  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R259835DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 237.1 lumens  
Efficiency: N/A  
Efficacy: 65.9 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275018  
CATALOG NUMBER: P3AS02R259835DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1275018  
 CATALOG NUMBER: P3AS02R259835DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	94	92	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	92	90	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	90	87	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	88	85	83
8	95	89	85	82	94	88	85	82	88	84	82	87	84	82	86	83	81	86	83	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	81	80	84	81	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	82	80	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	253379
5°	235020
10°	182250
15°	91397
20°	30033
25°	11928
30°	4482
35°	1285
40°	573
45°	217
50°	205
55°	153
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 80°  
 Luminance: 253 cd/sqm



TEST NUMBER: P1275018  
 CATALOG NUMBER: P3AS02R259835DE010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.9	39.6
10°-20°	112.0	47.3
20°-30°	25.3	10.7
30°-40°	4.1	1.7
40°-50°	0.7	0.3
50°-60°	0.4	0.2
60°-70°	0.4	0.2
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.2	97.5
0°-40°	235.3	99.3
0°-60°	236.5	99.7
0°-90°	237.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	237.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1156	
5°	1068	94
15°	403	112
25°	49	25
35°	5	4
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1275018  
CATALOG NUMBER: P3AS02R259835DE010 E3D1MW


**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1155.5
1°	1153.7
2°	1144.4
3°	1127.2
4°	1101.4
5°	1067.7
6°	1027.4
7°	983.9
8°	934.0
9°	879.4
10°	818.5
11°	748.3
12°	667.5
13°	583.0
14°	492.3
15°	402.6
17.5°	229.4
20°	128.7
22.5°	77.6
25°	49.3
27.5°	30.4
30°	17.7
32.5°	9.3
35°	4.8
37.5°	3.2
40°	2.0
42.5°	1.3
45°	0.7
47.5°	0.6
50°	0.6
52.5°	0.6
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1275018  
CATALOG NUMBER: P3AS02R259835DE010 E3D1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)