

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274225

Luminaire Tested: P3AS13R659830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 280.0 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274225

CATALOG NUMBER: P3AS13R659830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274225

CATALOG NUMBER: P3AS13R659830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49821
5°	49152
10°	47516
15°	44813
20°	41327
25°	37502
30°	33220
35°	28268
40°	22499
45°	15878
50°	9211
55°	5046
60°	4693
65°	4255
70°	3847
75°	3643
80°	3157
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15878 cd/sqm

TEST NUMBER: P1274225

CATALOG NUMBER: P3AS13R659830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.0	7.5
10°-20°	55.2	19.7
20°-30°	71.0	25.3
30°-40°	65.6	23.4
40°-50°	39.6	14.2
50°-60°	13.5	4.8
60°-70°	8.1	2.9
70°-80°	4.6	1.6
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	147.2	52.6
0°-40°	212.8	76.0
0°-60°	266.0	95.0
0°-90°	280.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	280.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	227	
5°	223	21
15°	197	55
25°	155	71
35°	106	66
45°	51	40
55°	13	14
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1274225

CATALOG NUMBER: P3AS13R659830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	227.2
2.5°	226.2
5°	223.3
7.5°	219.1
10°	213.4
12.5°	206.2
15°	197.4
17.5°	187.8
20°	177.1
22.5°	166.1
25°	155.0
27.5°	143.3
30°	131.2
32.5°	119.1
35°	105.6
37.5°	92.5
40°	78.6
42.5°	64.7
45°	51.2
47.5°	38.8
50°	27.0
52.5°	17.1
55°	13.2
57.5°	11.7
60°	10.7
62.5°	9.2
65°	8.2
67.5°	7.1
70°	6.0
72.5°	5.3
75°	4.3
77.5°	3.6
80°	2.5
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)