

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274234

Luminaire Tested: P3AS13R659830DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659830DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 503.0 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274234
CATALOG NUMBER: P3AS13R659830DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1274234
 CATALOG NUMBER: P3AS13R659830DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127863
5°	124675
10°	116097
15°	104041
20°	89864
25°	74738
30°	58946
35°	43687
40°	30114
45°	18669
50°	10132
55°	6384
60°	5394
65°	4877
70°	4167
75°	3728
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18669 cd/sqm



TEST NUMBER: P1274234
 CATALOG NUMBER: P3AS13R659830DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	10.5
10°-20°	127.4	25.3
20°-30°	140.8	28.0
30°-40°	102.3	20.3
40°-50°	47.9	9.5
50°-60°	16.1	3.2
60°-70°	9.3	1.9
70°-80°	4.9	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	320.8	63.8
0°-40°	423.2	84.1
0°-60°	487.2	96.9
0°-90°	503.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	503.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	583	
5°	566	53
15°	458	127
25°	309	141
35°	163	102
45°	60	48
55°	17	16
65°	9	9
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P1274234
CATALOG NUMBER: P3AS13R659830DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	583.1
2.5°	579.4
5°	566.4
7.5°	546.8
10°	521.4
12.5°	491.7
15°	458.3
17.5°	422.1
20°	385.1
22.5°	346.6
25°	308.9
27.5°	270.5
30°	232.8
32.5°	196.5
35°	163.2
37.5°	132.7
40°	105.2
42.5°	80.5
45°	60.2
47.5°	43.5
50°	29.7
52.5°	20.3
55°	16.7
57.5°	14.5
60°	12.3
62.5°	10.9
65°	9.4
67.5°	8.0
70°	6.5
72.5°	5.8
75°	4.4
77.5°	3.6
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)