

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275027

Luminaire Tested: P3AS02R259835DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259835DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 73.0 lumens
Efficiency: N/A
Efficacy: 20.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275027

CATALOG NUMBER: P3AS02R259835DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1275027

CATALOG NUMBER: P3AS02R259835DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17345
5°	16927
10°	15698
15°	13984
20°	12018
25°	10210
30°	8406
35°	6558
40°	4723
45°	2977
50°	1774
55°	1223
60°	1096
65°	1038
70°	962
75°	847
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2977 cd/sqm

TEST NUMBER: P1275027

CATALOG NUMBER: P3AS02R259835DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.1	9.8
10°-20°	17.1	23.4
20°-30°	19.3	26.4
30°-40°	15.3	20.9
40°-50°	7.7	10.6
50°-60°	3.1	4.2
60°-70°	2.0	2.7
70°-80°	1.1	1.5
80°-90°	0.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	43.5	59.6
0°-40°	58.8	80.6
0°-60°	69.6	95.3
0°-90°	73.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	73.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	79	
5°	77	7
15°	62	17
25°	42	19
35°	24	15
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275027

CATALOG NUMBER: P3AS02R259835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	79.1
1°	79.1
2°	78.8
3°	78.4
4°	77.8
5°	76.9
6°	75.9
7°	74.8
8°	73.5
9°	72.0
10°	70.5
11°	68.8
12°	67.1
13°	65.2
14°	63.4
15°	61.6
17.5°	56.5
20°	51.5
22.5°	46.7
25°	42.2
27.5°	37.7
30°	33.2
32.5°	28.9
35°	24.5
37.5°	20.4
40°	16.5
42.5°	12.8
45°	9.6
47.5°	7.2
50°	5.2
52.5°	3.9
55°	3.2
57.5°	2.9
60°	2.5
62.5°	2.3
65°	2.0
67.5°	1.7
70°	1.5
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.6
82.5°	0.5
85°	0.3
87.5°	0.1



TEST NUMBER: P1275027

CATALOG NUMBER: P3AS02R259835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)