

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274254

Luminaire Tested: P3AS13R709830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 17.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274254

CATALOG NUMBER: P3AS13R709830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274254

CATALOG NUMBER: P3AS13R709830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60039
5°	58948
10°	55577
15°	50443
20°	44127
25°	37212
30°	30486
35°	23637
40°	16917
45°	10699
50°	5356
55°	3250
60°	2807
65°	2594
70°	2308
75°	2118
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10699 cd/sqm

TEST NUMBER: P1274254

CATALOG NUMBER: P3AS13R709830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.0	9.8
10°-20°	61.8	24.2
20°-30°	70.4	27.5
30°-40°	55.1	21.5
40°-50°	27.0	10.6
50°-60°	8.3	3.2
60°-70°	4.9	1.9
70°-80°	2.6	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.2	61.4
0°-40°	212.3	82.9
0°-60°	247.6	96.7
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	268	25
15°	222	62
25°	154	70
35°	88	55
45°	34	27
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1274254

CATALOG NUMBER: P3AS13R709830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	273.8
2.5°	272.4
5°	267.8
7.5°	260.3
10°	249.6
12.5°	237.2
15°	222.2
17.5°	206.2
20°	189.1
22.5°	171.3
25°	153.8
27.5°	136.7
30°	120.4
32.5°	104.0
35°	88.3
37.5°	73.4
40°	59.1
42.5°	45.9
45°	34.5
47.5°	24.2
50°	15.7
52.5°	10.3
55°	8.5
57.5°	7.5
60°	6.4
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.6
72.5°	2.8
75°	2.5
77.5°	2.1
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)