

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274258

Luminaire Tested: P3AS13R709830DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709830DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 731.0 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274258
CATALOG NUMBER: P3AS13R709830DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1274258
 CATALOG NUMBER: P3AS13R709830DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141524
5°	139819
10°	135780
15°	130035
20°	121811
25°	110643
30°	95584
35°	76185
40°	55475
45°	36469
50°	17091
55°	5276
60°	5087
65°	4877
70°	4680
75°	4914
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36469 cd/sqm



TEST NUMBER: P1274258
 CATALOG NUMBER: P3AS13R709830DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	8.2
10°-20°	160.3	21.9
20°-30°	208.3	28.5
30°-40°	176.8	24.2
40°-50°	91.1	12.5
50°-60°	17.6	2.4
60°-70°	9.5	1.3
70°-80°	5.8	0.8
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.5	58.6
0°-40°	605.3	82.8
0°-60°	714.0	97.7
0°-90°	731.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	731.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	645	
5°	635	60
15°	573	160
25°	457	208
35°	285	177
45°	118	91
55°	14	18
65°	9	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1274258
CATALOG NUMBER: P3AS13R709830DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	645.4
2.5°	643.2
5°	635.2
7.5°	623.6
10°	609.8
12.5°	592.4
15°	572.8
17.5°	548.8
20°	522.0
22.5°	491.5
25°	457.3
27.5°	418.9
30°	377.5
32.5°	331.8
35°	284.6
37.5°	238.1
40°	193.8
42.5°	152.4
45°	117.6
47.5°	86.4
50°	50.1
52.5°	21.8
55°	13.8
57.5°	13.1
60°	11.6
62.5°	10.9
65°	9.4
67.5°	8.7
70°	7.3
72.5°	6.5
75°	5.8
77.5°	4.4
80°	3.6
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)