

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275063

Luminaire Tested: P3AS02R309835DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309835DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 152.0 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275063

CATALOG NUMBER: P3AS02R309835DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1275063

CATALOG NUMBER: P3AS02R309835DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35918
5°	35109
10°	32642
15°	29058
20°	24992
25°	21171
30°	17572
35°	13786
40°	9876
45°	6481
50°	3684
55°	2409
60°	2281
65°	2127
70°	1923
75°	1779
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6481 cd/sqm

TEST NUMBER: P1275063

CATALOG NUMBER: P3AS02R309835DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.8	9.7
10°-20°	35.6	23.4
20°-30°	40.1	26.4
30°-40°	32.0	21.1
40°-50°	16.4	10.8
50°-60°	6.2	4.1
60°-70°	4.1	2.7
70°-80°	2.2	1.4
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	90.5	59.5
0°-40°	122.5	80.6
0°-60°	145.1	95.5
0°-90°	152.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	152.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	164	
5°	160	15
15°	128	36
25°	88	40
35°	52	32
45°	21	16
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1275063

CATALOG NUMBER: P3AS02R309835DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	163.8
1°	163.8
2°	163.2
3°	162.3
4°	161.0
5°	159.5
6°	157.6
7°	155.2
8°	152.6
9°	149.6
10°	146.6
11°	143.2
12°	139.7
13°	136.0
14°	132.1
15°	128.0
17.5°	117.5
20°	107.1
22.5°	97.0
25°	87.5
27.5°	78.2
30°	69.4
32.5°	60.4
35°	51.5
37.5°	42.7
40°	34.5
42.5°	27.2
45°	20.9
47.5°	15.5
50°	10.8
52.5°	7.6
55°	6.3
57.5°	5.8
60°	5.2
62.5°	4.7
65°	4.1
67.5°	3.5
70°	3.0
72.5°	2.4
75°	2.1
77.5°	1.7
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.2



TEST NUMBER: P1275063

CATALOG NUMBER: P3AS02R309835DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)