

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275065

Luminaire Tested: P3AS02R309835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 59.0 lumens
Efficiency: N/A
Efficacy: 16.4 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275065
CATALOG NUMBER: P3AS02R309835DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1275065
 CATALOG NUMBER: P3AS02R309835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80				80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74				74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70				70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65				65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61				61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55				55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20152
5°	19524
10°	17590
15°	14552
20°	11271
25°	8444
30°	6128
35°	4096
40°	2519
45°	1489
50°	921
55°	726
60°	658
65°	519
70°	449
75°	424
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1489 cd/sqm



TEST NUMBER: P1275065
 CATALOG NUMBER: P3AS02R309835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.2	13.8
10°-20°	17.7	29.9
20°-30°	16.1	27.2
30°-40°	9.7	16.5
40°-50°	3.9	6.6
50°-60°	1.7	2.9
60°-70°	1.0	1.8
70°-80°	0.6	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	41.9	71.0
0°-40°	51.6	87.5
0°-60°	57.2	97.0
0°-90°	59.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	59.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	92	
5°	89	8
15°	64	18
25°	35	16
35°	15	10
45°	5	4
55°	2	2
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1275065
CATALOG NUMBER: P3AS02R309835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	91.9
1°	91.9
2°	91.5
3°	90.8
4°	89.9
5°	88.7
6°	87.3
7°	85.7
8°	83.7
9°	81.4
10°	79.0
11°	76.3
12°	73.4
13°	70.4
14°	67.2
15°	64.1
17.5°	56.0
20°	48.3
22.5°	41.2
25°	34.9
27.5°	29.3
30°	24.2
32.5°	19.6
35°	15.3
37.5°	11.7
40°	8.8
42.5°	6.4
45°	4.8
47.5°	3.6
50°	2.7
52.5°	2.1
55°	1.9
57.5°	1.6
60°	1.5
62.5°	1.2
65°	1.0
67.5°	0.9
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.5
80°	0.3
82.5°	0.2
85°	0.2
87.5°	0.1



TEST NUMBER: P1275065
CATALOG NUMBER: P3AS02R309835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)