

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274315

Luminaire Tested: P3AS17R209830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 925.0 lumens
Efficiency: N/A
Efficacy: 45.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274315

CATALOG NUMBER: P3AS17R209830DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1274315

CATALOG NUMBER: P3AS17R209830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228797
5°	222694
10°	204850
15°	180319
20°	154643
25°	129927
30°	105029
35°	79906
40°	56849
45°	37523
50°	23266
55°	15292
60°	13902
65°	12816
70°	12053
75°	10929
80°	10355
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37523 cd/sqm

TEST NUMBER: P1274315

CATALOG NUMBER: P3AS17R209830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.6	10.1
10°-20°	221.1	23.9
20°-30°	245.4	26.5
30°-40°	187.2	20.2
40°-50°	95.9	10.4
50°-60°	39.4	4.3
60°-70°	24.6	2.7
70°-80°	13.8	1.5
80°-90°	4.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.2	60.6
0°-40°	747.4	80.8
0°-60°	882.7	95.4
0°-90°	925.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	925.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1043	
5°	1012	94
15°	794	221
25°	537	245
35°	298	187
45°	121	96
55°	40	39
65°	25	25
75°	13	14
85°	4	4
90°	0	

TEST NUMBER: P1274315

CATALOG NUMBER: P3AS17R209830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1043.4
1°	1044.6
2°	1039.9
3°	1034.0
4°	1024.6
5°	1011.7
6°	996.4
7°	980.0
8°	962.3
9°	941.2
10°	920.0
12.5°	858.9
15°	794.3
17.5°	728.5
20°	662.7
22.5°	596.9
25°	537.0
27.5°	477.1
30°	414.8
32.5°	356.0
35°	298.5
37.5°	247.9
40°	198.6
42.5°	156.3
45°	121.0
47.5°	91.7
50°	68.2
52.5°	50.5
55°	40.0
57.5°	36.4
60°	31.7
62.5°	28.2
65°	24.7
67.5°	21.2
70°	18.8
72.5°	15.3
75°	12.9
77.5°	10.6
80°	8.2
82.5°	5.9
85°	3.5
87.5°	1.2
90°	0.0

(END OF REPORT)