

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275097

Luminaire Tested: P3AS02R359835DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359835DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 196.0 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275097

CATALOG NUMBER: P3AS02R359835DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1275097

CATALOG NUMBER: P3AS02R359835DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98852
5°	95003
10°	82786
15°	63406
20°	42424
25°	25671
30°	14736
35°	8245
40°	4380
45°	2264
50°	1092
55°	841
60°	833
65°	675
70°	705
75°	593
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2264 cd/sqm

TEST NUMBER: P1275097

CATALOG NUMBER: P3AS02R359835DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	20.0
10°-20°	76.1	38.8
20°-30°	49.8	25.4
30°-40°	20.2	10.3
40°-50°	6.1	3.1
50°-60°	2.1	1.1
60°-70°	1.4	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.2	84.3
0°-40°	185.4	94.6
0°-60°	193.5	98.7
0°-90°	196.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	196.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	451	
5°	432	39
15°	279	76
25°	106	50
35°	31	20
45°	7	6
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275097

CATALOG NUMBER: P3AS02R359835DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	450.8
1°	450.1
2°	448.0
3°	443.9
4°	439.1
5°	431.6
6°	422.3
7°	411.8
8°	400.1
9°	386.7
10°	371.8
11°	355.2
12°	337.8
13°	318.4
14°	300.0
15°	279.3
17.5°	229.1
20°	181.8
22.5°	139.8
25°	106.1
27.5°	79.1
30°	58.2
32.5°	42.7
35°	30.8
37.5°	21.8
40°	15.3
42.5°	10.6
45°	7.3
47.5°	4.8
50°	3.2
52.5°	2.4
55°	2.2
57.5°	2.1
60°	1.9
62.5°	1.7
65°	1.3
67.5°	1.1
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.6
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1275097

CATALOG NUMBER: P3AS02R359835DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)