

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274404

Luminaire Tested: P3AS17R359830DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274404  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359830DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 762.0 lumens  
Efficiency: N/A  
Efficacy: 37.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274404  
CATALOG NUMBER: P3AS17R359830DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1274404  
 CATALOG NUMBER: P3AS17R359830DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80	80	80	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	61	61	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57	57	57	57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	244937
5°	238894
10°	218411
15°	185381
20°	146756
25°	111006
30°	80797
35°	54636
40°	33577
45°	19289
50°	11599
55°	9405
60°	8245
65°	7316
70°	6027
75°	5931
80°	5935
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19289 cd/sqm



TEST NUMBER: P1274404  
 CATALOG NUMBER: P3AS17R359830DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.3	13.2
10°-20°	225.1	29.5
20°-30°	210.6	27.6
30°-40°	128.9	16.9
40°-50°	50.8	6.7
50°-60°	22.4	2.9
60°-70°	13.9	1.8
70°-80°	7.4	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.0	70.3
0°-40°	664.9	87.3
0°-60°	738.1	96.9
0°-90°	762.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	762.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1117	
5°	1085	100
15°	817	225
25°	459	211
35°	204	129
45°	62	51
55°	25	22
65°	14	14
75°	7	7
85°	2	3
90°	0	



TEST NUMBER: P1274404  
CATALOG NUMBER: P3AS17R359830DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1117.0
1°	1118.1
2°	1114.6
3°	1107.6
4°	1097.0
5°	1085.3
6°	1070.0
7°	1052.4
8°	1031.3
9°	1007.8
10°	980.9
11°	952.7
12°	922.2
13°	889.3
14°	853.0
15°	816.6
17.5°	722.7
20°	628.9
22.5°	538.5
25°	458.8
27.5°	384.8
30°	319.1
32.5°	258.1
35°	204.1
37.5°	156.0
40°	117.3
42.5°	84.5
45°	62.2
47.5°	44.6
50°	34.0
52.5°	28.2
55°	24.6
57.5°	21.1
60°	18.8
62.5°	16.4
65°	14.1
67.5°	11.7
70°	9.4
72.5°	8.2
75°	7.0
77.5°	5.9
80°	4.7
82.5°	3.5
85°	2.3
87.5°	1.2



TEST NUMBER: P1274404  
CATALOG NUMBER: P3AS17R359830DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)