

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275154

Luminaire Tested: P3AS02R459835DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459835DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 209.0 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275154

CATALOG NUMBER: P3AS02R459835DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1275154

CATALOG NUMBER: P3AS02R459835DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78481
5°	76645
10°	70451
15°	59705
20°	46321
25°	32373
30°	20408
35°	12019
40°	6784
45°	3318
50°	1160
55°	918
60°	921
65°	882
70°	833
75°	763
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3318 cd/sqm

TEST NUMBER: P1275154

CATALOG NUMBER: P3AS02R459835DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.2	15.4
10°-20°	72.2	34.6
20°-30°	61.3	29.3
30°-40°	29.3	14.0
40°-50°	8.8	4.2
50°-60°	2.2	1.1
60°-70°	1.7	0.8
70°-80°	1.0	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.8	79.3
0°-40°	195.0	93.3
0°-60°	206.1	98.6
0°-90°	209.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	209.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	358	
5°	348	32
15°	263	72
25°	134	61
35°	45	29
45°	11	9
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275154

CATALOG NUMBER: P3AS02R459835DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	357.9
2.5°	355.7
5°	348.2
7.5°	335.3
10°	316.4
12.5°	291.4
15°	263.0
17.5°	231.4
20°	198.5
22.5°	165.0
25°	133.8
27.5°	105.4
30°	80.6
32.5°	60.6
35°	44.9
37.5°	33.1
40°	23.7
42.5°	16.4
45°	10.7
47.5°	6.0
50°	3.4
52.5°	2.6
55°	2.4
57.5°	2.2
60°	2.1
62.5°	1.9
65°	1.7
67.5°	1.5
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)