

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275179

Luminaire Tested: P3AS02R509835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 68.0 lumens
Efficiency: N/A
Efficacy: 18.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275179

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1275179

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		76
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19779
5°	19238
10°	17746
15°	15596
20°	13068
25°	10355
30°	7596
35°	5220
40°	3321
45°	1861
50°	989
55°	841
60°	746
65°	675
70°	577
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1861 cd/sqm

TEST NUMBER: P1275179

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.1	11.9
10°-20°	19.0	28.0
20°-30°	19.5	28.6
30°-40°	12.4	18.2
40°-50°	4.9	7.2
50°-60°	2.0	2.9
60°-70°	1.3	1.9
70°-80°	0.6	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	46.6	68.5
0°-40°	59.0	86.7
0°-60°	65.9	96.8
0°-90°	68.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	68.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	90	
5°	87	8
15°	69	19
25°	43	19
35°	20	12
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275179

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	90.2
2.5°	89.5
5°	87.4
7.5°	84.1
10°	79.7
12.5°	74.5
15°	68.7
17.5°	62.5
20°	56.0
22.5°	49.4
25°	42.8
27.5°	36.2
30°	30.0
32.5°	24.5
35°	19.5
37.5°	15.3
40°	11.6
42.5°	8.6
45°	6.0
47.5°	4.0
50°	2.9
52.5°	2.5
55°	2.2
57.5°	1.9
60°	1.7
62.5°	1.5
65°	1.3
67.5°	1.1
70°	0.9
72.5°	0.7
75°	0.6
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)