

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275183

Luminaire Tested: P3AS02R509835DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509835DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 210.0 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275183

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1275183

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66859
5°	65507
10°	61366
15°	54938
20°	46227
25°	35276
30°	22940
35°	13599
40°	7843
45°	3938
50°	1467
55°	1147
60°	1053
65°	986
70°	962
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3938 cd/sqm

TEST NUMBER: P1275183

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.7	13.2
10°-20°	66.9	31.9
20°-30°	65.7	31.3
30°-40°	33.1	15.8
40°-50°	10.4	5.0
50°-60°	2.7	1.3
60°-70°	1.9	0.9
70°-80°	1.2	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.3	76.3
0°-40°	193.3	92.1
0°-60°	206.5	98.3
0°-90°	210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	210.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	305	
5°	298	28
15°	242	67
25°	146	66
35°	51	33
45°	13	10
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275183

CATALOG NUMBER: P3AS02R509835DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	304.9
2.5°	303.0
5°	297.6
7.5°	287.9
10°	275.6
12.5°	259.7
15°	242.0
17.5°	221.4
20°	198.1
22.5°	172.9
25°	145.8
27.5°	117.1
30°	90.6
32.5°	68.2
35°	50.8
37.5°	37.5
40°	27.4
42.5°	19.4
45°	12.7
47.5°	7.3
50°	4.3
52.5°	3.2
55°	3.0
57.5°	2.6
60°	2.4
62.5°	2.2
65°	1.9
67.5°	1.7
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)