

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274464

Luminaire Tested: P3AS17R459830DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459830DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1314.1 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274464

CATALOG NUMBER: P3AS17R459830DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1274464

CATALOG NUMBER: P3AS17R459830DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88		
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83		
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78		
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74		
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70		
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66		
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62		
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	493447
5°	481883
10°	442989
15°	375348
20°	291225
25°	203576
30°	128248
35°	75489
40°	42709
45°	20777
50°	7232
55°	5849
60°	5657
65°	5500
70°	5257
75°	4999
80°	4420
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20777 cd/sqm

TEST NUMBER: P1274464

CATALOG NUMBER: P3AS17R459830DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.7	15.4
10°-20°	454.0	34.6
20°-30°	385.6	29.3
30°-40°	183.9	14.0
40°-50°	55.4	4.2
50°-60°	14.1	1.1
60°-70°	10.5	0.8
70°-80°	6.2	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1042.2	79.3
0°-40°	1226.1	93.3
0°-60°	1295.6	98.6
0°-90°	1314.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1314.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2250	
5°	2189	203
15°	1653	454
25°	841	386
35°	282	184
45°	67	55
55°	15	14
65°	11	10
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1274464

CATALOG NUMBER: P3AS17R459830DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2250.3
2.5°	2236.2
5°	2189.2
7.5°	2108.1
10°	1989.5
12.5°	1832.0
15°	1653.4
17.5°	1454.8
20°	1248.0
22.5°	1037.6
25°	841.4
27.5°	662.8
30°	506.5
32.5°	380.7
35°	282.0
37.5°	208.0
40°	149.2
42.5°	103.4
45°	67.0
47.5°	37.6
50°	21.2
52.5°	16.5
55°	15.3
57.5°	14.1
60°	12.9
62.5°	11.8
65°	10.6
67.5°	9.4
70°	8.2
72.5°	7.1
75°	5.9
77.5°	4.7
80°	3.5
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)