

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274489

Luminaire Tested: P3AS17R509830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 425.0 lumens
Efficiency: N/A
Efficacy: 20.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274489

CATALOG NUMBER: P3AS17R509830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274489

CATALOG NUMBER: P3AS17R509830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		76
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123609
5°	120273
10°	110909
15°	97549
20°	81604
25°	64721
30°	47476
35°	32632
40°	20753
45°	11598
50°	6277
55°	5276
60°	4561
65°	4203
70°	3719
75°	3389
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11598 cd/sqm

TEST NUMBER: P1274489

CATALOG NUMBER: P3AS17R509830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	11.9
10°-20°	119.0	28.0
20°-30°	121.7	28.6
30°-40°	77.2	18.2
40°-50°	30.7	7.2
50°-60°	12.5	2.9
60°-70°	8.0	1.9
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.3	68.5
0°-40°	368.5	86.7
0°-60°	411.7	96.9
0°-90°	425.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	425.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	564	
5°	546	51
15°	430	119
25°	268	122
35°	122	77
45°	37	31
55°	14	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1274489

CATALOG NUMBER: P3AS17R509830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	563.7
2.5°	559.7
5°	546.4
7.5°	525.7
10°	498.1
12.5°	465.3
15°	429.7
17.5°	390.6
20°	349.7
22.5°	308.9
25°	267.5
27.5°	226.1
30°	187.5
32.5°	153.0
35°	121.9
37.5°	95.5
40°	72.5
42.5°	53.5
45°	37.4
47.5°	25.3
50°	18.4
52.5°	15.5
55°	13.8
57.5°	12.1
60°	10.4
62.5°	9.2
65°	8.1
67.5°	6.9
70°	5.8
72.5°	4.6
75°	4.0
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)