

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275212

Luminaire Tested: P3AS02R559835DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559835DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 203.0 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275212

CATALOG NUMBER: P3AS02R559835DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1275212

CATALOG NUMBER: P3AS02R559835DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55741
5°	55184
10°	53283
15°	49262
20°	42494
25°	33558
30°	23801
35°	15366
40°	9217
45°	5210
50°	2797
55°	994
60°	877
65°	882
70°	833
75°	763
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5210 cd/sqm

TEST NUMBER: P1275212

CATALOG NUMBER: P3AS02R559835DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.6	11.6
10°-20°	60.0	29.6
20°-30°	62.9	31.0
30°-40°	36.7	18.1
40°-50°	13.7	6.8
50°-60°	3.2	1.6
60°-70°	1.7	0.8
70°-80°	1.0	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	146.4	72.1
0°-40°	183.1	90.2
0°-60°	200.1	98.6
0°-90°	203.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	203.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	254	
5°	251	24
15°	217	60
25°	139	63
35°	57	37
45°	17	14
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275212

CATALOG NUMBER: P3AS02R559835DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	254.2
2.5°	253.5
5°	250.7
7.5°	246.2
10°	239.3
12.5°	229.6
15°	217.0
17.5°	200.9
20°	182.1
22.5°	161.1
25°	138.7
27.5°	115.8
30°	94.0
32.5°	74.3
35°	57.4
37.5°	43.6
40°	32.2
42.5°	23.1
45°	16.8
47.5°	12.1
50°	8.2
52.5°	4.7
55°	2.6
57.5°	2.2
60°	2.0
62.5°	1.9
65°	1.7
67.5°	1.5
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)