

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274523

Luminaire Tested: P3AS17R559830DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559830DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 855.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274523

CATALOG NUMBER: P3AS17R559830DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1274523

CATALOG NUMBER: P3AS17R559830DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232591
5°	226744
10°	210795
15°	187720
20°	159521
25°	128741
30°	98142
35°	69814
40°	46058
45°	27321
50°	16034
55°	9863
60°	8771
65°	7939
70°	6796
75°	5931
80°	5935
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27321 cd/sqm

TEST NUMBER: P1274523

CATALOG NUMBER: P3AS17R559830DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	11.2
10°-20°	229.3	26.8
20°-30°	242.8	28.4
30°-40°	164.1	19.2
40°-50°	71.9	8.4
50°-60°	25.7	3.0
60°-70°	15.1	1.8
70°-80°	7.9	0.9
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.7	66.4
0°-40°	731.8	85.6
0°-60°	829.4	97.0
0°-90°	855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1061	
5°	1030	96
15°	827	229
25°	532	243
35°	261	164
45°	88	72
55°	26	26
65°	15	15
75°	7	8
85°	2	3
90°	0	

TEST NUMBER: P1274523

CATALOG NUMBER: P3AS17R559830DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1060.7
2.5°	1052.5
5°	1030.1
7.5°	993.7
10°	946.7
12.5°	890.4
15°	826.9
17.5°	756.5
20°	683.6
22.5°	607.3
25°	532.1
27.5°	458.1
30°	387.6
32.5°	320.7
35°	260.8
37.5°	206.7
40°	160.9
42.5°	121.0
45°	88.1
47.5°	64.6
50°	47.0
52.5°	32.9
55°	25.8
57.5°	23.5
60°	20.0
62.5°	17.6
65°	15.3
67.5°	12.9
70°	10.6
72.5°	9.4
75°	7.0
77.5°	5.9
80°	4.7
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)