

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275378

Luminaire Tested: P3AS05R259835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 121.0 lumens
Efficiency: N/A
Efficacy: 16.8 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275378
CATALOG NUMBER: P3AS05R259835DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1275378
 CATALOG NUMBER: P3AS05R259835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43922
5°	42153
10°	36918
15°	29671
20°	22799
25°	17251
30°	12458
35°	8272
40°	5009
45°	2915
50°	1876
55°	1529
60°	1316
65°	1193
70°	962
75°	932
80°	758
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2915 cd/sqm



TEST NUMBER: P1275378
 CATALOG NUMBER: P3AS05R259835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.4	14.4
10°-20°	36.1	29.9
20°-30°	32.7	27.0
30°-40°	19.6	16.2
40°-50°	7.8	6.4
50°-60°	3.6	3.0
60°-70°	2.2	1.8
70°-80°	1.1	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	86.3	71.3
0°-40°	105.9	87.5
0°-60°	117.3	96.9
0°-90°	121.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	121.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	200	
5°	192	17
15°	131	36
25°	71	33
35°	31	20
45°	9	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1275378
CATALOG NUMBER: P3AS05R259835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	200.3
1°	200.3
2°	199.4
3°	197.3
4°	194.7
5°	191.5
6°	187.3
7°	182.6
8°	177.1
9°	171.7
10°	165.8
11°	159.0
12°	152.0
13°	145.1
14°	138.1
15°	130.7
17.5°	113.4
20°	97.7
22.5°	83.6
25°	71.3
27.5°	59.8
30°	49.2
32.5°	39.6
35°	30.9
37.5°	23.6
40°	17.5
42.5°	12.8
45°	9.4
47.5°	7.2
50°	5.5
52.5°	4.5
55°	4.0
57.5°	3.4
60°	3.0
62.5°	2.5
65°	2.3
67.5°	1.9
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.6
82.5°	0.4
85°	0.4
87.5°	0.2



TEST NUMBER: P1275378
CATALOG NUMBER: P3AS05R259835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)