

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274576

Luminaire Tested: P3AS17R659830DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R659830DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 399.0 lumens  
Efficiency: N/A  
Efficacy: 19.6 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274576  
CATALOG NUMBER: P3AS17R659830DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1274576  
 CATALOG NUMBER: P3AS17R659830DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	101417
5°	98899
10°	92094
15°	82543
20°	71290
25°	59302
30°	46767
35°	34639
40°	23873
45°	14792
50°	8051
55°	5046
60°	4298
65°	3891
70°	3334
75°	2965
80°	2904
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14792 cd/sqm



TEST NUMBER: P1274576  
 CATALOG NUMBER: P3AS17R659830DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.7	10.5
10°-20°	101.0	25.3
20°-30°	111.7	28.0
30°-40°	81.2	20.3
40°-50°	38.0	9.5
50°-60°	12.8	3.2
60°-70°	7.4	1.9
70°-80°	3.9	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.5	63.8
0°-40°	335.7	84.1
0°-60°	386.5	96.9
0°-90°	399.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	399.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	462	
5°	449	42
15°	364	101
25°	245	112
35°	129	81
45°	48	38
55°	13	13
65°	8	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1274576  
CATALOG NUMBER: P3AS17R659830DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	462.5
2.5°	459.6
5°	449.3
7.5°	433.7
10°	413.6
12.5°	390.0
15°	363.6
17.5°	334.8
20°	305.5
22.5°	275.0
25°	245.1
27.5°	214.6
30°	184.7
32.5°	155.9
35°	129.4
37.5°	105.3
40°	83.4
42.5°	63.9
45°	47.7
47.5°	34.5
50°	23.6
52.5°	16.1
55°	13.2
57.5°	11.5
60°	9.8
62.5°	8.6
65°	7.5
67.5°	6.3
70°	5.2
72.5°	4.6
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)