

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274581

Luminaire Tested: P3AS17R659830DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659830DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 814.0 lumens
Efficiency: N/A
Efficacy: 39.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274581

CATALOG NUMBER: P3AS17R659830DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1274581

CATALOG NUMBER: P3AS17R659830DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206913
5°	201760
10°	187883
15°	168378
20°	145426
25°	120951
30°	95382
35°	70698
40°	48720
45°	30205
50°	16409
55°	10322
60°	8771
65°	7939
70°	6796
75°	5931
80°	5935
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30205 cd/sqm

TEST NUMBER: P1274581

CATALOG NUMBER: P3AS17R659830DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.2	10.5
10°-20°	206.1	25.3
20°-30°	227.9	28.0
30°-40°	165.6	20.3
40°-50°	77.6	9.5
50°-60°	26.1	3.2
60°-70°	15.1	1.9
70°-80°	7.9	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.2	63.8
0°-40°	684.8	84.1
0°-60°	788.5	96.9
0°-90°	814.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	814.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	944	
5°	917	85
15°	742	206
25°	500	228
35°	264	166
45°	97	78
55°	27	26
65°	15	15
75°	7	8
85°	2	3
90°	0	

TEST NUMBER: P1274581

CATALOG NUMBER: P3AS17R659830DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	943.6
2.5°	937.7
5°	916.6
7.5°	884.9
10°	843.8
12.5°	795.7
15°	741.7
17.5°	683.0
20°	623.2
22.5°	561.0
25°	499.9
27.5°	437.7
30°	376.7
32.5°	318.0
35°	264.1
37.5°	214.8
40°	170.2
42.5°	130.3
45°	97.4
47.5°	70.4
50°	48.1
52.5°	32.9
55°	27.0
57.5°	23.5
60°	20.0
62.5°	17.6
65°	15.3
67.5°	12.9
70°	10.6
72.5°	9.4
75°	7.0
77.5°	5.9
80°	4.7
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)