

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275453

Luminaire Tested: P3AS05R409835DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409835DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 541.0 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275453

CATALOG NUMBER: P3AS05R409835DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1275453

CATALOG NUMBER: P3AS05R409835DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275767
5°	273761
10°	266595
15°	238140
20°	157910
25°	59157
30°	15825
35°	6184
40°	2233
45°	1054
50°	307
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1054 cd/sqm

TEST NUMBER: P1275453

CATALOG NUMBER: P3AS05R409835DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	21.7
10°-20°	278.0	51.4
20°-30°	126.1	23.3
30°-40°	16.3	3.0
40°-50°	2.8	0.5
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	521.4	96.4
0°-40°	537.7	99.4
0°-60°	540.9	100.0
0°-90°	541.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	541.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1258	
5°	1244	117
15°	1049	278
25°	244	126
35°	23	16
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1275453

CATALOG NUMBER: P3AS05R409835DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1257.6
1°	1256.8
2°	1254.9
3°	1252.1
4°	1248.5
5°	1243.7
6°	1238.2
7°	1231.4
8°	1223.1
9°	1211.7
10°	1197.3
11°	1180.5
12°	1157.9
13°	1130.1
14°	1093.7
15°	1049.0
16°	992.0
17°	927.1
18°	849.0
19°	766.7
20°	676.7
21°	586.7
22°	498.1
23°	409.8
24°	323.1
25°	244.5
26°	181.1
27°	132.6
28°	99.6
29°	77.5
30°	62.5
31°	51.7
32°	43.2
32.5°	39.4
33°	35.6
34°	29.0
35°	23.1
36°	18.2
37°	14.4
37.5°	12.9
38°	11.4
39°	9.5
40°	7.8
42.5°	5.1
45°	3.4



TEST NUMBER: P1275453

CATALOG NUMBER: P3AS05R409835DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.1
50°	0.9
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)