

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274632

Luminaire Tested: P3AS20R159830D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274632
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159830D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 941.0 lumens
Efficiency: N/A
Efficacy: 34.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274632
CATALOG NUMBER: P3AS20R159830D010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1274632
 CATALOG NUMBER: P3AS20R159830D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	405779
5°	375038
10°	299416
15°	226176
20°	172238
25°	131258
30°	94014
35°	61355
40°	37613
45°	22731
50°	15113
55°	11699
60°	10043
65°	8717
70°	7822
75°	7795
80°	5809
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22731 cd/sqm



TEST NUMBER: P1274632
 CATALOG NUMBER: P3AS20R159830D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.9	16.0
10°-20°	278.5	29.6
20°-30°	247.9	26.3
30°-40°	146.7	15.6
40°-50°	60.2	6.4
50°-60°	28.3	3.0
60°-70°	17.2	1.8
70°-80°	9.1	1.0
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.3	72.0
0°-40°	824.0	87.6
0°-60°	912.4	97.0
0°-90°	941.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	941.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1850	
5°	1704	151
15°	996	278
25°	542	248
35°	229	147
45°	73	60
55°	31	28
65°	17	17
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P1274632
CATALOG NUMBER: P3AS20R159830D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1850.5
1°	1845.9
2°	1832.2
3°	1804.7
4°	1758.8
5°	1703.8
6°	1644.2
7°	1573.9
8°	1500.6
9°	1425.7
10°	1344.7
12.5°	1159.8
15°	996.3
17.5°	855.7
20°	738.1
22.5°	634.2
25°	542.5
27.5°	453.8
30°	371.3
32.5°	296.4
35°	229.2
37.5°	175.7
40°	131.4
42.5°	97.8
45°	73.3
47.5°	56.5
50°	44.3
52.5°	36.7
55°	30.6
57.5°	26.0
60°	22.9
62.5°	19.9
65°	16.8
67.5°	15.3
70°	12.2
72.5°	10.7
75°	9.2
77.5°	6.1
80°	4.6
82.5°	3.1
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)