

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274653

Luminaire Tested: P3AS20R209830D010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209830D010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1581.0 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274653

CATALOG NUMBER: P3AS20R209830D010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1274653

CATALOG NUMBER: P3AS20R209830D010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1216394
5°	1105742
10°	817197
15°	505519
20°	288682
25°	164816
30°	92419
35°	50299
40°	27537
45°	15164
50°	8870
55°	6423
60°	6008
65°	5552
70°	4873
75°	5168
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15164 cd/sqm

TEST NUMBER: P1274653

CATALOG NUMBER: P3AS20R209830D010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	435.0	27.5
10°-20°	621.0	39.3
20°-30°	324.1	20.5
30°-40°	125.3	7.9
40°-50°	40.7	2.6
50°-60°	16.0	1.0
60°-70°	10.6	0.7
70°-80°	6.2	0.4
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1380.1	87.3
0°-40°	1505.4	95.2
0°-60°	1562.1	98.8
0°-90°	1581.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1581.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5547	
5°	5023	435
15°	2227	621
25°	681	324
35°	188	125
45°	49	41
55°	17	16
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1274653

CATALOG NUMBER: P3AS20R209830D010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5547.2
1°	5536.5
2°	5470.9
3°	5370.1
4°	5214.3
5°	5023.4
6°	4797.3
7°	4546.8
8°	4256.6
9°	3974.1
10°	3670.1
12.5°	2917.2
15°	2226.8
17.5°	1666.3
20°	1237.1
22.5°	916.4
25°	681.2
27.5°	502.5
30°	365.0
32.5°	264.2
35°	187.9
37.5°	135.9
40°	96.2
42.5°	68.7
45°	48.9
47.5°	35.1
50°	26.0
52.5°	19.9
55°	16.8
57.5°	15.3
60°	13.7
62.5°	12.2
65°	10.7
67.5°	9.2
70°	7.6
72.5°	7.6
75°	6.1
77.5°	4.6
80°	3.1
82.5°	3.1
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)