

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275541

Luminaire Tested: P3AS05R559835DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1275541  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R559835DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 98CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 206.0 lumens  
Efficiency: N/A  
Efficacy: 28.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275541

CATALOG NUMBER: P3AS05R559835DE010 E3DL1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1275541

CATALOG NUMBER: P3AS05R559835DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 73  | 63  | 57  | 53  | 72  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 56574 |
| 5°  | 55998 |
| 10° | 54063 |
| 15° | 49989 |
| 20° | 43124 |
| 25° | 34066 |
| 30° | 24156 |
| 35° | 15580 |
| 40° | 9360  |
| 45° | 5272  |
| 50° | 2831  |
| 55° | 994   |
| 60° | 921   |
| 65° | 882   |
| 70° | 833   |
| 75° | 763   |
| 80° | 758   |
| 85° | 503   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5272 cd/sqm

TEST NUMBER: P1275541

CATALOG NUMBER: P3AS05R559835DE010 E3DL1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 23.9   | 11.6      |
| 10°-20°   | 60.9   | 29.6      |
| 20°-30°   | 63.8   | 31.0      |
| 30°-40°   | 37.2   | 18.1      |
| 40°-50°   | 13.9   | 6.8       |
| 50°-60°   | 3.3    | 1.6       |
| 60°-70°   | 1.7    | 0.8       |
| 70°-80°   | 1.0    | 0.5       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 148.6  | 72.1      |
| 0°-40°    | 185.8  | 90.2      |
| 0°-60°    | 203.0  | 98.6      |
| 0°-90°    | 206.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 206.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 258 |      |
| 5°  | 254 | 24   |
| 15° | 220 | 61   |
| 25° | 141 | 64   |
| 35° | 58  | 37   |
| 45° | 17  | 14   |
| 55° | 3   | 3    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1275541

CATALOG NUMBER: P3AS05R559835DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 258.0 |
| 2.5°  | 257.2 |
| 5°    | 254.4 |
| 7.5°  | 249.8 |
| 10°   | 242.8 |
| 12.5° | 233.0 |
| 15°   | 220.2 |
| 17.5° | 203.9 |
| 20°   | 184.8 |
| 22.5° | 163.5 |
| 25°   | 140.8 |
| 27.5° | 117.5 |
| 30°   | 95.4  |
| 32.5° | 75.4  |
| 35°   | 58.2  |
| 37.5° | 44.2  |
| 40°   | 32.7  |
| 42.5° | 23.4  |
| 45°   | 17.0  |
| 47.5° | 12.3  |
| 50°   | 8.3   |
| 52.5° | 4.7   |
| 55°   | 2.6   |
| 57.5° | 2.3   |
| 60°   | 2.1   |
| 62.5° | 1.9   |
| 65°   | 1.7   |
| 67.5° | 1.5   |
| 70°   | 1.3   |
| 72.5° | 1.1   |
| 75°   | 0.9   |
| 77.5° | 0.8   |
| 80°   | 0.6   |
| 82.5° | 0.4   |
| 85°   | 0.2   |
| 87.5° | 0.2   |
| 90°   | 0.0   |

(END OF REPORT)