

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274666

Luminaire Tested: P3AS20R259830D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259830D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1944.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274666
CATALOG NUMBER: P3AS20R259830D010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1274666

CATALOG NUMBER: P3AS20R259830D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2078408
5°	1927686
10°	1494962
15°	749607
20°	246281
25°	97917
30°	36740
35°	10627
40°	4809
45°	1892
50°	1569
55°	1185
60°	1360
65°	1608
70°	962
75°	1271
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 80°
 Luminance: 1894 cd/sqm



TEST NUMBER: P1274666
 CATALOG NUMBER: P3AS20R259830D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	770.3	39.6
10°-20°	919.0	47.3
20°-30°	207.2	10.7
30°-40°	33.6	1.7
40°-50°	6.1	0.3
50°-60°	3.3	0.2
60°-70°	2.9	0.1
70°-80°	1.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1896.4	97.6
0°-40°	1930.0	99.3
0°-60°	1939.4	99.8
0°-90°	1944.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1944.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9478	
5°	8758	770
15°	3302	919
25°	405	207
35°	40	34
45°	6	6
55°	3	3
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1274666
CATALOG NUMBER: P3AS20R259830D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	9478.3
1°	9463.1
2°	9386.7
3°	9246.2
4°	9033.9
5°	8757.5
6°	8427.6
7°	8070.2
8°	7660.9
9°	7213.4
10°	6714.0
11°	6138.2
12°	5475.3
13°	4781.9
14°	4038.1
15°	3302.0
17.5°	1881.6
20°	1055.4
22.5°	636.9
25°	404.7
27.5°	248.9
30°	145.1
32.5°	76.4
35°	39.7
37.5°	26.0
40°	16.8
42.5°	10.7
45°	6.1
47.5°	4.6
50°	4.6
52.5°	4.6
55°	3.1
57.5°	3.1
60°	3.1
62.5°	3.1
65°	3.1
67.5°	3.1
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1274666
CATALOG NUMBER: P3AS20R259830D010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)